


# Nickel

## Solvent Extraction Technology



 **BASF**

We create chemistry

# BASF technology for the recovery of nickel from laterites

Nickel laterite ores are becoming an increasingly important source of nickel and cobalt. BASF solvent extraction reagents are used in a nickel production plant, Queensland Nickel Inc. (QNI), to extract nickel from ammonia solutions. LIX® 87QN reagent was developed to fit into a QNI-developed nickel recovery process based on a modified Caron process. While operating, Cawse Nickel Operations used a flowsheet originally conceived by BASF and further developed by Cawse, for the recovery of nickel from laterite ores using High Pressure Acid Leaching (HPAL).

The basic elements of the front half of the process used at Cawse are High Pressure Acid Leaching (HPAL) of the laterite, solid liquid separation, pH adjustment to remove iron and then the subsequent precipitation of the base metals nickel, copper, zinc and cobalt as hydroxides. The refinery portion of the plant re-leached the crystalline base metal hydroxide with ammonia under oxidizing conditions, followed by solvent extraction with LIX® 84-INS and electrowinning of the nickel. Cobalt is recovered from the nickel-depleted raffinate by precipitation of cobalt sulfide using sodium hydrosulphide. The cobalt product can be sold or further treated to produce high-purity cobalt metal.


## Advantages of the Cawse flowsheet

1. The process has been proven on an industrial scale producing 8,000 tonnes/year nickel cathode.
2. The front half of the process produces an intermediate crystalline base metal hydroxide that can either be sold to other nickel producers or further treated to produce high-purity nickel cathode and cobalt sulfide. The hydroxide intermediate can be stockpiled to provide a steady nickel feed to the refinery portion of the plant, even when the HPAL circuit is shut down.
3. The hydroxide precipitation step followed by an ammonia re-leach is largely selective for Ni, Co, Cu and Zn while rejecting troublesome Mn and Cr from the SX feed.
4. Use of MgO as the base in the hydroxide precipitation step minimizes the formation of gypsum in downstream processing.
5. The nickel concentration of the ammonia leach solution can be controlled to minimize the size of the nickel SX plant. Typically, the ammonia leach solution has a concentration of 10–20 g/l nickel.
6. The final nickel product is a high-purity electrowon cathode, a readily marketable product. Cobalt is recovered as marketable cobalt sulfide product. There is also the potential to produce nickel sulfate.
7. Ammonia is recycled, resulting in a low ammonia consumption rate per tonne of nickel produced.
8. Metal containing intermediates are recycled resulting in very high metal recovery.
9. The process employs only one SX circuit and one extractant type. This removes the possibility of cross contamination of circuit organics.





## PRODUCTION OF BASE METAL HYDROXIDE INTERMEDIATE



For more information, please reference:

The Recovery of Nickel from High-Pressure Acid Leach Solutions Using Mixed Hydroxide Product – LIX® 84-INS Technology  
by Murdoch Mackenzie, Michael Vimig and Angus Feather

Nickel Laterite Processing: Recovery of Nickel from Ammoniacal Leach Liquors  
by J.M.W. Mackenzie, MJ. Virnig, G.A. Wolfe and R.D.Boley

Ammoniacal Solvent Extraction at Queensland Nickel, Process Installation and Operation  
by J.G. Reid and MJ. Price

Schematic flowsheet for the HPAL process to recover nickel at Cawse Nickel Operations



Cawse Nickel plant




### Cobalt stripping, copper stripping and circuit organic re-oxidation

To control the concentration of cobalt and copper on the circuit organic, a bleed stream of the circuit organic is treated to remove copper and cobalt, both of which can be recovered. If there is sufficient copper present, cathode copper or copper sulfate can be produced. Cobalt is recovered as cobalt sulfide. After copper and cobalt removal, the organic bleed stream passes to re-oxidation to minimize solvent extraction reagent consumption.

Aspects of the BASF Nickel technology are covered by US Patent 5,976,218.

Major operating parameters of the SX-EW circuit

### AMMONIA LEACH – LIX® 84-INS NICKEL SX – ELECTROWINNING



## Europe

### **BASF SE**

Mining Solutions  
Carl-Bosch-Str. 38  
67056 Ludwigshafen  
Germany  
Phone: +49 621 60 0  
Fax: +49 621 60 42525

## North America

### **BASF Corporation**

3231 E Valencia Road  
Tucson, AZ 85706  
US  
Phone: +1 520 629 3208  
Fax: +1 520 573 2998

## South America

### **BASF CHILE S.A.**

Av. Carrascal N° 3851  
Quinta Normal  
Santiago  
Chile  
Phone: +56 2 2640 7000  
Fax: +56 2 775 3095

## Africa

### **BASF South Africa (Pty) Ltd.**

852 Sixteenth Road  
Midrand, P.O. Box 2801  
Halfway House 1685  
South Africa  
Phone: +27 11 203 2400  
Fax: +27 11 203 2431

## Australia

### **BASF Australia Ltd.**

Level 12, 28 Freshwater Place  
VIC 3006, Southbank  
Australia  
Phone: +613 8855 6600  
Fax: +613 8855 6511

**For further information:**  
[miningsolutions@basf.com](mailto:miningsolutions@basf.com)  
[www.mining-solutions.basf.com](http://www.mining-solutions.basf.com)

The descriptions, designs, data and information contained herein are presented in good faith, and are based on BASF's current knowledge and experience. They are provided for guidance only, and do not constitute the agreed contractual quality of the product or a part of BASF's terms and conditions of sale. Because many factors may affect processing or application/use of the product, BASF recommends that the reader carry out its own investigations and tests to determine the suitability of a product for its particular purpose prior to use. It is the responsibility of the recipient of product to ensure that any proprietary rights and existing laws and legislation are observed. No warranties of any kind, either express or implied, including, but not limited to, warranties of merchantability or fitness for a particular purpose, are made regarding products described or designs, data or information set forth herein, or that the products, descriptions, designs, data or information may be used without infringing the intellectual property rights of others. Any descriptions, designs, data and information given in this publication may change without prior information. The descriptions, designs, data, and information furnished by BASF hereunder are given gratis and BASF assumes no obligation or liability for the descriptions, designs, data or information given or results obtained, all such being given and accepted at the reader's risk. (08/2019)

® = registered trademark of BASF SE